


nVent CADDY Speed Link Y-Hook with Eyelet Extension



VLASTNOSTI

Double hook offers easy attachment to basket tray, cable tray or lighting

Convenient design allows one hook to be temporarily detached for maintenance or to add cables to the tray

Y-design provides improved stability

Spring latch helps provide secure connection



SPECIFIKACE

Table 1/2



Katalogové číslo	Article Number	Materiál	Povrchová úprava	Static Load Safety Factor	Wire Rope Diameter	Wire Rope "Y" Length (YL)
SLD2YH500	196015	Ocel	Electrogalvaniz ed	5:1	2 mm	0.5m

Table 2/2

Katalogové číslo	Article Number	A	B	C	Static Load
SLD2YH500	196015	58.4 mm	22.9 mm	6 mm	440N

DALŠÍ PODROBNOSTI O PRODUKTU

nVent CADDY Speed Link locking device not included.



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

