

nVent CADDY Superklip



VLASTNOSTI

Closes and locks automatically when the pipe, tube or cable is inserted



One-piece clamp for fast and convenient installation

Fasten with either wood screw, dual threaded screw with or without collar, nail with collar, threaded rod, mounting plate or shot-fire bracket

Materiál: Xenoy®
Temperature: -25 to 90 °C

SPECIFIKACE

Katalogové číslo	Article Number	Outer Diameter (OD)	Copper Tube Size	B	C	Static Load
389001	389001	11.8 - 14.3 mm	3/8"	17.2 mm	29.9 mm	160N
389002	389002	14.3 - 16.8 mm	1/2"	19.5 mm	32 mm	175N
389003	389003	16.8 - 19.5 mm	5/8"	20 mm	35.4 mm	190N
389004	389004	19.5 - 21.8 mm		20 mm	39.4 mm	200N
389005	389005	21.8 - 24.8 mm	3/4"	20 mm	42 mm	215N
389006	389006	24.8 - 27.8 mm		20.2 mm	45.1 mm	240N
389007	389007	27.8 - 31.2 mm	1"	20.2 mm	48.9 mm	260N
389008	389008	31.2 - 35.5 mm	1 1/4"	21 mm	54.4 mm	300N
389009	389009	35.5 - 39.5 mm	1 1/4"	21 mm	59.4 mm	320N
389011	389011	39.5 - 43.5 mm	1 1/2"	21 mm	64.2 mm	360N
389013	389013	50.5 - 55.5 mm	2"	23 mm	78.7 mm	400N
389017	389017	7.8 - 9.5 mm	1/4"	17.1 mm	26.4 mm	135N
389018	389018	9.5 - 11.8 mm	1/4"	17.1 mm	26.4 mm	150N



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

