

Strut Beam Clamp with U-Bolt



VLASTNOSTI

Complete with U-bolt and nuts

Requires installation in pairs

SPECIFIKACE

Table 1/2

Katalogové číslo	Article Number	Materiál	Povrchová úprava	Strut Type	Rod Size (RS)	Flange Thickness (FT)
ZTA601HD	387701	Ocel	Hot-Dip Galvanized	A (41 x 41 mm), C (21 x 41 mm), CC (41 x 41 mm)	10	18 mm Max
ZTA601S6	387710	Stainless Steel 316 (EN 1.4401)		A (41 x 41 mm), C (21 x 41 mm), CC (41 x 41 mm)	10	18 mm Max
ZTA602HD	388006	Ocel	Hot-Dip Galvanized	A (41 x 41 mm), AA (83 x 41 mm), D (62 x 41 mm), E (83 x 41 mm)	10	18 mm Max
ZTA603HD	388066	Ocel	Hot-Dip Galvanized	DD (124 x 41 mm)	10	18 mm Max

Table 2/2


Katalogové číslo	Article Number	Width (W)	Thickness (T)	A	B	C	Static Load
ZTA601HD	387701	80 mm	6 mm	24 mm	45 mm	95 mm	5000N
ZTA601S6	387710	80 mm	6 mm	24 mm	45 mm	110 mm	5000N
ZTA602HD	388006	80 mm	6 mm	24 mm	45 mm	140 mm	5000N

Katalogové číslo	Article Number	Width (W)	Thickness (T)	A	B	C	Static Load
ZTA603HD	388066	80 mm	6 mm	24 mm	45 mm	180 mm	5000N

DALŠÍ PODROBNOSTI O PRODUKTU

Static Load is based on one pair of Strut Beam Clamps.

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

