

Threaded Stud

VLASTNOSTI

Pre-cut lengths of threaded rod




Materiál: Ocel
Povrchová úprava: Electrogalvanized
Quality Class: 4.6

SPECIFIKACE

Katalogové číslo	Article Number	Rod Size (RS)	Length (L)
051M10025	400345	M10	25mm
051M10040	400346	M10	40mm
051M10060	400347	M10	60mm
051M10080	400349	M10	80mm
051M10090	593505	M10	90mm
051M10100	400351	M10	100mm
051M10150	593516	M10	150mm
051M8025	400336	M8	25mm
051M8040	400337	M8	40mm
051M8060	400338	M8	60mm
051M8070	593465	M8	70mm
051M8080	400340	M8	80mm

Katalogové číslo	Article Number	Rod Size (RS)	Length (L)
051M8100	400342	M8	100mm
051M8120	593476	M8	120mm
051M8150	593477	M8	150mm

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

