

U-Channel Cantilever Arm, Perforated with Brace

VLASTNOSTI

U-Profile cantilever arm with brace

Perforated/slotted design



Materiál: Ocel
Povrchová úprava: Hot-Dip Galvanized



SPECIFIKACE

Katalogové číslo	Article Number	Length (L)	Height (H)	Width (W)	Hole Size (HS)
CUCS0250HD	312110	250mm	230 mm	40 mm	13 mm
CUCS0300HD	312120	300mm	230 mm	40 mm	13 mm
CUCS0400HD	312140	400mm	230 mm	40 mm	13 mm
CUCS0500HD	312160	500mm	230 mm	40 mm	13 mm
CUCS0600HD	312170	600mm	230 mm	40 mm	13 mm
CUCS0800HD	312180	800mm	400 mm	40 mm	13 mm
CUCS1000HD	312190	1000mm	400 mm	40 mm	13 mm
CUCS1300HD	312195	1300mm	400 mm	40 mm	13 mm

A: 30 mm
B: 30 mm
C: 50 mm
D: 11 mm

E: 36 mm
Thickness (T): 3 mm
Diameter (Ø): 11 mm

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/GRDDT

