


Uniklip Variable Riser



VLASTNOSTI

Creates a quick and easy vertical pathway transition

Provides optimal support for high-performance low voltage and data cables

Innovative UNIKLIP installation system that installs up to three times faster

IEC 61537 load rating and earthing compliant

No field cutting or modifications required; just drop it in and keep installing the cable tray

Eliminates safety related concerns around field cutting



Tool-free, integrated couplers with Uniklip

Materiál: Ocel
Povrchová úprava: Pregalvanized



SPECIFIKACE

Katalogové číslo	Article Number	Width (W)	Height (H)	Angle (a)	A	B	C
PCT50X050VR90	850200	50 mm	437 mm	90 ° Max	296 mm	49 mm	91 mm
PCT50X075VR90	850210	75 mm	437 mm	90 ° Max	296 mm	49 mm	91 mm
PCT50X100VR90	850220	100 mm	437 mm	90 ° Max	296 mm	49 mm	91 mm
PCT50X150VR90	850230	150 mm	437 mm	90 ° Max	296 mm	49 mm	91 mm
PCT50X225VR90	850240	225 mm	437 mm	90 ° Max	296 mm	49 mm	91 mm
PCT50X300VR90	850250	300 mm	437 mm	90 ° Max	296 mm	49 mm	91 mm
PCT50X450VR90	850260	450 mm	437 mm	90 ° Max	296 mm	49 mm	91 mm
PCT50X500VR90	850270	500 mm	437 mm	90 ° Max	296 mm	49 mm	91 mm
PCT50X600VR90	850280	600 mm	437 mm	90 ° Max	296 mm	49 mm	91 mm



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

