


Wire Basket Tray Polymer Insert



The nVent CADDY Wire Basket Tray Polymer Insert utilizes a flame-retardant polymer to envelop the entire tray- providing bottom, side and cover protection. Available options include a flat bottom or a prescored version to the tray depth for coverage of the bottom and sides.

VLASTNOSTI

Standard black finish for use with divider posts

Polymer insert rolls into the tray bottom

Multiple color options to coordinate with cable tray selection


Barva: Black
Materiál: Polymer

SPECIFIKACE

Katalogové číslo	Height (H)	Width (W)	Length (L)	Sides Included	Unit Weight
WBTFORM06BA		143 mm	3048mm	No	0.03 kg
WBTFORM08BA		193.8 mm	3048mm	No	0.04 kg
WBTFORM12BA		295.4 mm	3048mm	No	0.06 kg
WBTFORM18BA		447.8 mm	3048mm	No	0.09 kg
WBTFORM24BA		600.2 mm	3048mm	No	0.12 kg
WBTFORM2X12BA	50.8 mm	295.4 mm	3048mm	Yes	0.08 kg
WBTFORM2X18BA	50.8 mm	447.8 mm	3048mm	Yes	0.11 kg
WBTFORM2X24BA	50.8 mm	600.2 mm	3048mm	Yes	0.14 kg
WBTFORM2X4BA	50.8 mm	92.2 mm	3048mm	Yes	0.04 kg
WBTFORM2X6BA	50.8 mm	143 mm	3048mm	Yes	0.05 kg
WBTFORM2X8BA	50.8 mm	193.8 mm	3048mm	Yes	0.06 kg
WBTFORM4X12BA	101.6 mm	295.4 mm	3048mm	Yes	0.1 kg
WBTFORM4X16BA	101.6 mm	397 mm	3048mm	Yes	0.12 kg
WBTFORM4X18BA	101.6 mm	447.8 mm	3048mm	Yes	0.13 kg
WBTFORM4X24BA	101.6 mm	600.2 mm	3048mm	Yes	0.16 kg
WBTFORM4X4BA	101.6 mm	92.2 mm	3048mm	Yes	0.06 kg

Katalogové číslo	Height (H)	Width (W)	Length (L)	Sides Included	Unit Weight
WBTFORM4X6BA	101.6 mm	143 mm	3048mm	Yes	0.07 kg
WBTFORM6X12BA	152.4 mm	295.4 mm	3048mm	Yes	0.12 kg
WBTFORM6X18BA	152.4 mm	447.8 mm	3048mm	Yes	0.16 kg
WBTFORM6X24BA	152.4 mm	600.2 mm	3048mm	Yes	0.18 kg

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

