

DR Symmetric Profile



VLASTNOSTI

Rapid assembly of all kinds of frameworks

High mechanical resistance

High corrosion resistance

Conforms to EN 60715 and 50022 and DIN 46277

RoHS compliant


Materiál: Ocel
Povrchová úprava: Electrogalvanized



SPECIFIKACE

Katalogové číslo	Article Number	Height (H)	Width (W)	Length (L)	Thickness (T)	A	Unit Weight
DR15X2M	557900	35 mm	15 mm	2000mm	1.5 mm	4 mm	1.3 kg
DR15X3M	557910	35 mm	15 mm	3000mm	1.5 mm	4 mm	1.95 kg
DR5-5X2M	557700	15 mm	5.5 mm	2000mm	1 mm	2.25 mm	0.33 kg
DR7X2M	557800	35 mm	7.5 mm	2000mm	1 mm	4 mm	0.66 kg
DR7X3M	557810	35 mm	7.5 mm	3000mm	1 mm	4 mm	0.99 kg

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.