

PCB Plain Copper Busbar



VLASTNOSTI

Heavy-duty power connection

Circuit breaker, generator and prefabricated power network conductor

Alternative to large and multiple cables

Earth/ground connection

Power distribution

Rounded edges

Materiál: Copper



SPECIFIKACE

Table 1/2


Katalogové číslo	Article Number	Width (W)	Thickness (T)	Length (L)	Unit Weight
PCB-1M-12X4	550780	12 mm	4 mm	990mm	0.43 kg
PCB-2M-100X10	549750	100 mm	10 mm	2000mm	17.8 kg
PCB-2M-100X5	549640	100 mm	5 mm	2000mm	8.9 kg
PCB-2M-120X10	549760	120 mm	10 mm	2000mm	21.4 kg
PCB-2M-12X4	550790	12 mm	4 mm	1985mm	0.85 kg
PCB-2M-12X5	550770	12 mm	5 mm	1985mm	1.06 kg
PCB-2M-25X5	549600	25 mm	5 mm	2000mm	2.2 kg
PCB-2M-30X10	549700	30 mm	10 mm	2000mm	5.5 kg
PCB-2M-40X10	549710	40 mm	10 mm	2000mm	7.1 kg
PCB-2M-50X10	549720	50 mm	10 mm	2000mm	8.9 kg
PCB-2M-50X5	549610	50 mm	5 mm	2000mm	4.5 kg
PCB-2M-60X10	549730	60 mm	10 mm	2000mm	10.7 kg
PCB-2M-63X5	549620	63 mm	5 mm	2000mm	5.6 kg

Katalogové číslo	Article Number	Width (W)	Thickness (T)	Length (L)	Unit Weight
PCB-2M-80X10	549740	80 mm	10 mm	2000mm	14.2 kg
PCB-2M-80X5	549630	80 mm	5 mm	2000mm	7.1 kg
PCB-4M-100X10	550930	100 mm	10 mm	4000mm	35.6 kg
PCB-4M-100X5	550670	100 mm	5 mm	4000mm	17.8 kg
PCB-4M-120X10	550940	120 mm	10 mm	4000mm	42.8 kg
PCB-4M-160X10	550950	160 mm	10 mm	4000mm	57 kg
PCB-4M-20X5	550600	20 mm	5 mm	4000mm	3.56 kg

Table 2/2

Katalogové číslo	Article Number	Width (W)	Thickness (T)	Length (L)	Unit Weight
PCB-4M-25X5	550610	25 mm	5 mm	4000mm	4.45 kg
PCB-4M-30X10	550970	30 mm	10 mm	4000mm	10.69 kg
PCB-4M-30X5	550620	30 mm	5 mm	4000mm	5.34 kg
PCB-4M-40X10	550980	40 mm	10 mm	4000mm	14.25 kg
PCB-4M-40X5	550630	40 mm	5 mm	4000mm	7.12 kg
PCB-4M-50X10	550900	50 mm	10 mm	4000mm	17.8 kg
PCB-4M-50X5	550640	50 mm	5 mm	4000mm	8.9 kg
PCB-4M-60X10	550910	60 mm	10 mm	4000mm	21.35 kg
PCB-4M-60X5	550650	60 mm	5 mm	4000mm	10.68 kg
PCB-4M-80X10	550920	80 mm	10 mm	4000mm	28.5 kg
PCB-4M-80X5	550660	80 mm	5 mm	4000mm	14.24 kg

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

