

Universal Connecting Bar



nVent ERIFLEX Connecting, Earthing and Neutral Busbars are used to connect several earthing conductors within a panel and can be used in a variety of different applications including switchgear and control equipment, electrical equipment, for wind and solar power generation and in data centers. This Universal Connecting Bar can be used as a 450A current rating IEC for power distribution.

VLASTNOSTI

Easy to wire with a hexagonal key

Design allows for visual inspection of conductor and confirmation of connection

For use with punched or threaded copper busbar

High fill ratio allows output connection with or without terminal

Quick and easy installation

RoHS compliant



SPECIFIKACE

Table 1/2



Katalogové číslo	CB7X16
Article Number	553150
Materiál	Brass
Max Current Rating	450A
Number of Tunnel Connections	7
Conductor Size, IEC	(7) 1.5 - 16 mm ² Stranded

Katalogové číslo	CB7X16
Ferrule Conductor Size, IEC	(7) 1.5 - 16 mm ²
Conductor Size, UL	(7) #10 - #6 Solid (7) #8 - #4 Stranded
Hloubka (D)	12.5mm
Height (H)	31 mm
Width (W)	68 mm
A	9 mm
B	4 mm
Torque (TQ)	3.5 N·m

Table 2/2

Katalogové číslo	CB7X16
Unit Weight	0.08 kg

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

