


19" Front Panel for Thermostat With Digital Display, 1 U



19" Front Panel for Thermostat With Digital Display, 1 U

VLASTNOSTI

19" Front Panel, 1 U, with cut-out for thermostat with digital display

Accessory Type: Front panel



SPECIFIKACE

Table 1/3

Katalogové číslo	Typ	Mounting	EMC Shielding	Materiál	Front Finish	Rear Finish
30118-267	19" Front Panel	Screw-on Front	No	Hliník	Anodized	Anodized
30118-315	19" Front Panel	Screw-on Front	No	Hliník	Painted	Painted
30118-360	19" Front Panel	Screw-on Front	No	Hliník	Painted	Painted

Table 2/3

Katalogové číslo	Kód barvy	Rack Height	Výška	Rack Width	Šířka	Hloubka
30118-267		1U	35mm		76mm	3mm
30118-315	RAL 7035	1U	43mm	95HP	483mm	3mm
30118-360	RAL 7021	1U	43mm	95HP	483mm	3mm

Table 3/3

Katalogové číslo	Množství v balení	Povrchová úprava
30118-267	1	Anodized
30118-315	1	Strukturovaný Práškový

Katalogové číslo	Množství v balení	Povrchová úprava
30118-360	1	Strukturovaný Práškový

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.