


Assembly Parts for Rugged Components



Assembly parts with thread-locking compound for rugged Side Panel, horizontal rail, cover plates, rear angle.

VLASTNOSTI

Screws for the following fixings: Rugged side panel - horizontal rail, Rugged side panel - cover plate, Rugged side panel - rear angle

Produktová řada: EuropacPRO
Product Type: Assembly Kit



SPECIFIKACE

Katalogové číslo	Typ	Length	Množství v balení	Thread Size	Povrchová úprava	Materiál	Works With
24566-100	Countersunk Screw	18mm	100	M4		Stainless Steel	Subracks
24566-101	Countersunk Screw	14mm	100	M4		Stainless Steel	Subracks
24560-140	Square Nut		100		Pozinkovaná Ocel	Ocel	Subracks
24566-102	Panhead Screw	14mm	100	M4		Stainless Steel	Subracks
24566-103	Panhead Screw	10mm	100	M4		Stainless Steel	Subracks
24566-104	Panhead Screw	8mm	100	M4		Stainless Steel	Subracks
24566-105	Countersunk Screw	7mm	100	M4		Stainless Steel	Subracks
24566-106	Countersunk Screw	10mm	100	M4		Stainless Steel	Subracks

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

