


Collar Screw, Cross Recess/Slotted



Integrated load spreading, replaces separate washer.
Improved joint consistency (less variation from washer misalignment) Better vibration resistance, especially with serrated collars

VLASTNOSTI

For assembly of partial width front panels and plug-in units

For EuropacPRO and RatiopacPRO

Cross Recess / Slotted combines advantages of both imprints: it offers a high level of torque to achieve quick and easy installation and enhances rotational leverage. It is convenient to use while offering universal tool compatibility.

Product Type: Screw

Typ: Screw



SPECIFIKACE

Table 1/3

Katalogové číslo	Diameter	Length	Materiál	Povrchová úprava	Množství v balení	Thread Size
21101-101		12.3mm	Ocel	Nickel Plated	100	M2.5
21101-906		12.3mm	Stainless Steel		100	M2.5
21101-102		12.3mm	Ocel	Zinc Plated, Black	100	M2.5
21101-323		11mm			100	M2.5
21102-026	2.5mm	12.3mm	Ocel	Nickel Plated	100	M2.5

Table 2/3

Katalogové číslo	Hloubka	Výška	Šířka	Works With	Thread Length	Thread Type
21101-101	14.3mm	5mm	5mm	Front Panels	12.3mm	Metric
21101-906				Front Panels	12.3mm	
21101-102	14.3mm	5mm	5mm	Front Panels	12.3mm	Metric
21101-323				Front Panels		
21102-026				Frame Type Plug-In Unit, Cassettes	3mm	

Table 3/3

Katalogové číslo	Torque	Certifications
21101-101	0.3N·m	RoHS
21101-906	0.3N·m	RoHS
21101-102	0.3N·m	RoHS
21101-323	0.3N·m	
21102-026	0.3N·m	

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

