

Edge-DC-48VDC Power Distribution Unit



The nVent Edge-DC-48VDC Power Distribution Unit (DCDU) is designed to provide efficient, safe, and reliable power distribution for telecom and edge computing environments. This unit ensures optimal performance and protection for your critical infrastructure.

VLASTNOSTI

High Power Capacity: Robust 250 A 48 VDC input

Blind Mating Capability: Supports switched and metered DC Modules from 10 A to 60 A

Circuit Breaker Trip Alarm: Immediate notification for enhancing response times

Compliance with Industry Standards: UL/CE certified

Hot Swappable Breakers with Precise Metering: For energy, power, current, and voltage at both input and device levels

Granular Control with Device Level Switching: Management of individual devices for optimized performance

Billing Grade Monitoring: Identification of potential system failures

Smart Alerting System: Informs about overcurrent, overvoltage, undervoltage, and other threshold breaches

Controller Interface: TCP or IP network connection

Local Management: Features front panel push-button to toggle module output. Panel status LED indicator quickly relays module information to local user



SPECIFIKACE

Table 1/2

Katalogové číslo	Product Type	Circuit Breaker	Circuit Breaker Quantity	Hloubka	Vstupní napětí DC	Metering Type
21280-001	Power Distributor	- 48 VDC 60 Amp, - 48 VDC 35 Amp	10	410mm	-48V min	Outlet
21280-002	Power Distributor	- 48 VDC 60 Amp, - 48 VDC 35 Amp	8	410mm	-48V min	Outlet
21280-003	Power Distributor	- 48 VDC 35 Amp	8	410mm	-48V min	Outlet

Table 2/2

Katalogové číslo	Number of Switched Outlets	Rack Height	Rack Width	Rated Current	Typ
21280-001	(2) 60 A, (8) 35 A	3U	84HP	250A	- 48 V DCDU

Katalogové číslo	Number of Switched Outlets	Rack Height	Rack Width	Rated Current	Typ
21280-002	(4) 60 A, (4) 35 A	3U	84HP	250A	- 48 V DCDU
21280-003	(8) 35 A	3U	84HP	250A	- 48 V DCDU

DALŠÍ PODROBNOSTI O PRODUKTU

For exact configuration please refer to the item(s) delivered table.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.