


Cooling Circuitry STD 3U 76TE mont. W/ QD

New

KATALOGOVÉ ČÍSLO

20740-050



The Easy Swap LFT Cooling Circuit is a "back-pack" cooling Unit for a 3U subrack rear area. With its width of 76 HP it allows an additional 8 HP front panel to be mounted aside for the mains power inlet to the subrack. Up to 3 Easy Swap Cold plates can be attached to the unit either by the Easy Swap LFT Direct Connection Set or the Quick Disconnect Set. It dissipates the heat of the Cold Plates with a heat exchanger and 2 low noise fans to the back.

VLASTNOSTI

Cooling Circuitry for up to 3 Easy Swap LFT Cold Plates

3 U height, 76 HP width. Can be mounted at the backside of a 3U subrack

Up to 600 W of cooling capacity at 50°C environmental temperature

Accepts demineralized water or Water Glycol mix (25% Glycol recommended)

Low noise fans and pump

Easy Swap LFT Cold Plates can be connected to Cooling Circuitry either with Direct Connection Set or Quick Disconnect Set



VLASTNOSTI PRODUKTU

Množství v balení: 1

Produktová řada: Liquid Board Cooling

Product Type: Conductor Block

Typ: Liquid Cooling Circuitry

Šířka: 383.8mm

Works With: Subracks

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched

from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DALŠÍ PODROBNOSTI O PRODUKTU

Please order the Cold Plates and Connection sets separately

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

