

Chassis Monitoring Module CMM

Obsolete

KATALOGOVÉ ČÍSLO

23207-022

Monitoring of voltage, temperatures and digital inputs.


VLASTNOSTI

Data bus for communication with the SCHROFF Fan Control Module (FCM)

Pluggable in 3 U Eurocard format

Inputs and outputs for VME and CPCI specific signals, further digital and LED outputs

Communication and remote control via RS 232 or Ethernet interface (10BaseT)



Status Monitor	Temp.
Voltage	CMM 23 °C
+3.3V	FCM 24 °C
+5.0V	Fan Speed
+12.0V	61 %
-12.0V	Fan Speed Settings
Temperature	T1 25 °C
CMM	T2 26 °C
FCM	Temp. Alarm
Fan Speed	CMM 40 °C
Fan 1	FCM 60 °C
Fan 2	
Fan 3	



VLASTNOSTI PRODUKTU

Product Type: System Module

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

