



$^{+/-}$ can be combined, $^{+/-}$ combinations not recommended

 Light profile	-	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile
 Light profile	+	 Light profile	+	 Light profile

34560-501

VLASTNOSTI

< 28 HP not printed

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings



VLASTNOSTI PRODUKTU

Rack Width: 195HP

Množství v balení: 1

Povrchová úprava: Anodized

Length: 1000mm

Materiál: Hliník

Produktová řada: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO

Product Type: Horizontal Rail

Typ: Heavy, ST

Works With: Subracks; Cases

Net Weight: 0.304kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DALŠÍ PODROBNOSTI O PRODUKTU

Delivery is in standard pack multiples. Pricing is per individual item.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.