

EuropacPRO Advanced EMC Side Panel Cover


Aluminium Side panel 3mm to increase the EMC shielding effect of the subrack by covering the not needed cut-outs.

VLASTNOSTI

Side panel covers for increased lateral RF shielding

Assembled on the outside of the standard side panel

Assembly material included



EMC Shielding:	Yes
Povrchová úprava:	Passivated
Materiál:	Hliník
Produktová řada:	EuropacPRO
Product Type:	Side Panel
Typ:	Type H
Works With:	Subracks



SPECIFIKACE

Table 1/2

Katalogové číslo	Rack Height	Hloubka	Množství v balení	Length	Balení
24563-255	3U	175mm	2	175mm	Pair
24563-256	3U	235mm	2	235mm	Pair
24563-257	3U	275mm	2	275mm	Pair
24563-258	3U	277.75mm	2	277.75mm	Pair
24563-259	3U	295mm	2	295mm	Pair
24563-260	3U	355mm	2	355mm	Pair
24563-261	3U	415mm	2	415mm	Pair
24563-262	3U	495mm	2	495mm	Pair
24563-265	4U	175mm	2	175mm	Pair
24563-266	4U	235mm	2	235mm	Pair
24563-267	4U	295mm	2	295mm	Pair
24563-268	4U	355mm	2	355mm	Pair
24563-269	4U	415mm	2	415mm	Pair
24563-270	4U	495mm	2	495mm	Pair

Katalogové číslo	Rack Height	Hloubka	Množství v balení	Length	Balení
24563-275	6U	175mm	2	175mm	Pair
24563-276	6U	235mm	2	235mm	Pair
24563-277	6U	275mm	2	275mm	Pair
24563-278	6U	277.75mm	2	277.75mm	Pair
24563-279	6U	295mm	2	295mm	Pair
24563-280	6U	355mm	2	355mm	Pair

Table 2/2

Katalogové číslo	Rack Height	Hloubka	Množství v balení	Length	Balení
24563-281	6U	415mm	2	415mm	Pair
24563-282	6U	495mm	2	495mm	Pair

DALŠÍ PODROBNOSTI O PRODUKTU

Side panel and 19" bracket are tox-cold welded together. toxen = Clinching technique, without add aids. This takes place with special tools and high pressure.

9 U version available on request.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

