

Guide Rail With Coding for CompactPCI/ VME64x, PC



New generation of With Coding type guide rails for PCBs or plug-in units. Forms a reliable interface between the subrack mechanics and the sub-assemblies. With the optimized design and the new high quality plastic material not just the stability was significantly increased, but also the fire safety properties improved. Which means the material ensures a low flammability, low smoke toxicity and density and fulfills the EN 45545-2 (Fire Safety in Railway Vehicle) requirements sets R22, R23 and R24 with the

VLASTNOSTI

NEW generation with coding type plastic guide rails for reliable retention of PCBs or plug-in units

Significantly increased stability, due to a optimized design and high quality material (PC)

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

"Halogen-Free", according to IEC 61249-2-21

Can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Can be bolted to the horizontal rails Type H and R for higher shock and vibration requirements

Optional ESD clip for an conductive contact between PCB and horizontal rail available

Storage temperature: from -40 °C ... 130 °C

Produktová řada:	EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO; Inpac
Product Type:	Guide Rail
Typ:	Coding
Works With:	Subracks; Cases; 19" Chassis; Systems



SPECIFIKACE

Katalogové číslo	Board Depth	Groove Width	Barva	Materiál	Množství v balení	Complies With	Povrchová úprava
64568-089	160mm	2	Red	Fiber-Reinforced Plastic	1	EN 45545-2	

Katalogové číslo	Board Depth	Groove Width	Barva	Materiál	Množství v balení	Complies With	Povrchová úprava
64568-090	160mm	2	Grey	Fiber-Reinforced Plastic	1	EN 45545-2	
24568-331	280mm	2.5	Red, Silver	Fiber-Reinforced Plastic, Hliník	10	EN 45545-2	Anodized
24568-332	340mm	2.5	Red, Silver	Fiber-Reinforced Plastic, Hliník	10	EN 45545-2	Anodized
24568-341	280mm	2.5	Grey, Silver	Fiber-Reinforced Plastic, Hliník	10	EN 45545-2	Anodized
24568-342	340mm	2.5	Grey, Silver	Fiber-Reinforced Plastic, Hliník	10	EN 45545-2	
24568-356	160mm	2	Red	Fiber-Reinforced Plastic	10	EN 45545-2	
24568-357	70mm	2	Red	Fiber-Reinforced Plastic	10	EN 45545-2	
24568-358	160mm	2	Grey	Fiber-Reinforced Plastic	10	EN 45545-2	
24568-360	70mm	2	Grey	Fiber-Reinforced Plastic	10	EN 45545-2	
64568-085	70mm	2	Red	Fiber-Reinforced Plastic	1	EN 45545-2	
64568-086	70mm	2	Grey	Fiber-Reinforced Plastic	1	EN 45545-2	
64568-091	220mm	2	Red	Fiber-Reinforced Plastic	1	EN 45545-2	
64568-092	220mm	2	Grey	Fiber-Reinforced Plastic	1	EN 45545-2	
64568-111	220mm	2.5	Red, Silver	Fiber-Reinforced Plastic, Hliník	1	EN 45545-2	
64568-109	160mm	2.5	Red, Silver	Fiber-Reinforced Plastic, Hliník	1	EN 45545-2	
64568-110	160mm	2.5	Grey, Silver	Fiber-Reinforced Plastic, Hliník	1	EN 45545-2	
64568-112	220mm	2.5	Grey, Silver	Fiber-Reinforced Plastic, Hliník	1	EN 45545-2	

DALŠÍ PODROBNOSTI O PRODUKTU

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.