


# Mounting Plate for 19" Case and Subrack



Mounting plate for heavy components or proprietary electronic assemblies. Suitable for RatiopacPRO/-AIR, CompacPRO and EuropacPRO.

Guide rails Type 4,4" and type strengthened cannot be used in combination with a mounting plate. Top / bottom cover which will be inserted into the groove of the light (type L) horizontal rails cannot be used in combination with a mounting plate.

## VLASTNOSTI

For assembly of heavy components

Mounting plate, full width: The mounting plate is as wide as the subrack/system case and is fixed to the side panels

Mounting plate, partial width: The partial width mounting plate fixed to the side panel by means of an assembly strip

The chassis plate can't be combined with EMC top- / bottom covers

**Materiál:** Hliník  
**Product Type:** Mounting Plate  
**Works With:** Subracks



## SPECIFIKACE

| Katalogové číslo | Rack Width | Množství v balení | Hloubka     | Produktová řada                               | Šířka        | Certifikace |
|------------------|------------|-------------------|-------------|-----------------------------------------------|--------------|-------------|
| 34562-750        | 42HP       | 1                 | 172.5m<br>m | EuropacPRO, CompacPRO, RatiopacPRO, PropacPRO | 217.99m<br>m | RoHS        |
| 34562-746        | 42HP       | 1                 | 112.5m<br>m | EuropacPRO, PropacPRO, RatiopacPRO, CompacPRO | 217.99m<br>m | RoHS        |
| 34562-754        | 42HP       | 1                 | 232.5m<br>m | EuropacPRO, RatiopacPRO, CompacPRO            | 217.99m<br>m | RoHS        |
| 34562-758        | 42HP       | 1                 | 292.2m<br>m | EuropacPRO, RatiopacPRO, CompacPRO            | 217.99m<br>m | RoHS        |
| 34562-752        | 84HP       | 1                 | 172.5m<br>m | EuropacPRO, CompacPRO, RatiopacPRO, PropacPRO | 431.35m<br>m | RoHS        |
| 34562-748        | 84HP       | 1                 | 112.5m<br>m | EuropacPRO, PropacPRO, RatiopacPRO, CompacPRO | 324.67m<br>m | RoHS        |
| 34562-756        | 84HP       | 1                 | 232.5m<br>m | EuropacPRO, RatiopacPRO, CompacPRO            | 431.35m<br>m | RoHS        |

| Katalogové číslo | Rack Width | Množství v balení | Hloubka     | Produktová řada                               | Šířka        | Certifikace |
|------------------|------------|-------------------|-------------|-----------------------------------------------|--------------|-------------|
| 34562-760        | 84HP       | 1                 | 292.5m<br>m | EuropacPRO, PropacPRO, RatiopacPRO, CompacPRO | 431.35m<br>m | RoHS        |
| 34562-749        | 28HP       | 1                 | 172.5m<br>m | EuropacPRO, RatiopacPRO, CompacPRO            | 146.88m<br>m | RoHS        |
| 34562-745        | 28HP       | 1                 | 112.5m<br>m | EuropacPRO, RatiopacPRO, CompacPRO            | 146.88m<br>m | RoHS        |
| 34562-753        | 28HP       | 1                 | 232.5m<br>m | EuropacPRO, RatiopacPRO, CompacPRO            | 146.88m<br>m | RoHS        |
| 34562-751        | 63HP       | 1                 | 172.5m<br>m | EuropacPRO, RatiopacPRO, CompacPRO, PropacPRO | 324.67m<br>m | RoHS        |
| 34562-747        | 63HP       | 1                 | 112.5m<br>m | EuropacPRO, PropacPRO, RatiopacPRO, CompacPRO | 324.67m<br>m | RoHS        |
| 34562-755        | 63HP       | 1                 | 232.5m<br>m | EuropacPRO, RatiopacPRO, CompacPRO            | 324.67m<br>m | RoHS        |
| 34562-759        | 63HP       | 1                 | 292.2m<br>m | EuropacPRO, RatiopacPRO, CompacPRO            | 324.67m<br>m | RoHS        |
| 34562-870        | 84HP       | 1                 | 352.5m<br>m | EuropacPRO                                    | 431.35m<br>m |             |
| 34562-871        | 84HP       | 1                 | 412.5m<br>m | EuropacPRO                                    | 431.35m<br>m |             |
| 34562-757        | 28HP       | 1                 | 292.2m<br>m | EuropacPRO, RatiopacPRO, CompacPRO            | 146.88m<br>m | RoHS        |

## DALŠÍ PODROBNOSTI O PRODUKTU

Please order assembly kit for mounting plate separately.

Other versions on request.

Fixing strips required for partial width, please order separately.

## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

