


MTCA.4 Front Panel



AdvancedTCA front panel (stainless steel) for textile gasketing. Shielded filler modules are used to close unused slots.

VLASTNOSTI

In accordance with MicroTCA.1 and MicroTCA.4 specifications

Shielded filler modules are used to close unused slots

Can be screwed on; is supported on the guide rail

Accessory Type:	Front panel
EMC Shielding:	Yes
Materiál:	Stainless Steel
Produktová řada:	AdvancedMC
Product Type:	Front Panel
Typ:	Front Panel



SPECIFIKACE

Table 1/2

Katalogové číslo	Výška	Rack Width	Množství v balení	Mounting	Gasket Type	Front Finish
21850-102	84.68mm		1	Screw-on Front	Textile EMC	Raw
21850-103	84.68mm		1	Screw-on Front	Textile EMC	Raw
20849-213	95mm	2HP	1	Screw-on Front	Textile EMC	Raw
20849-214	170mm	2HP	1	Screw-on Front	Textile EMC	Raw

Table 2/2

Katalogové číslo	Rear Finish	Hloubka	Šířka
21850-102	Raw	1mm	18.96mm
21850-103	Raw	1mm	28.98mm
20849-213	Raw	0.6mm	8.8mm
20849-214	Raw	0.6mm	8.8mm

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.