


Panhead Screw, Pozidriv



Good compromise between profile height and bearing area. Better load distribution than round heads. Compatible with automated assembly.

VLASTNOSTI

Phillips screw offers a high level of torque to achieve quick and easy installation. The Phillips screw drive is more stable with the help of four contact points and better performing with screwdrivers. But unlike other kinds of screw drives, the Phillips drive is designed to cam out in which screw drive slips out of the cross head once the torque is needed to drive the screw exceeds a certain amount to avoid over tightening.

Pozidriv has a set of 45° radial indentations from the main cross recess leading to 4 additional contact points and greater stabilization to provide a greater contact surface. As a result, it decrease cam-out and wear, which allows greater torque to be applied.

Materiál: Ocel
Product Type: Screw



SPECIFIKACE

Table 1/2

Katalogové číslo	Diameter	Length	Povrchová úprava	Množství v balení	Thread Size	Produktová řada
21100-788		12mm	Pozinkovaný a Ocel	100	M5	EuropacPRO
21120-150	5mm	10mm	Pozinkovaný a Ocel	100	M5	
21101-222		16mm	Nickel Plated	100	M2.5	Frame Type Plug-In Unit
21101-221		12mm	Nickel Plated	100	M2.5	Frame Type Plug-In Unit
21101-220		10mm	Nickel Plated	100	M2.5	Frame Type Plug-In Unit
21101-219		6mm	Nickel Plated	100	M2.5	Frame Type Plug-In Unit
21102-024	3mm	6mm	Pozinkovaný a Ocel	100	M3	

Katalogové číslo	Diameter	Length	Povrchová úprava	Množství v balení	Thread Size	Produktová řada
21100-021	6mm	16mm	Pozinkovaná Ocel	50	M6	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO
21100-022	6mm	16mm	Pozinkovaná Ocel	100	M6	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO
21101-314		5mm	Nickel Plated	100	M2.5	
21100-650	6mm	16mm	Zinc Plated, Black	100	M6	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO
21101-069		8mm	Nickel Plated	100	M2.5	Frame Type Plug-In Unit
21120-202	6mm	16mm	Pozinkovaná Ocel	50	M6	
21120-203	6mm	16mm	Pozinkovaná Ocel	100	M6	

Table 2/2

Katalogové číslo	Typ	Works With	Thread Length	Thread Type	Certifications
21100-788	Panhead Screw	Subracks	12mm		RoHS
21120-150	Coding Block	Cabinet	10mm		RoHS
21101-222	Panhead Screw	Backplanes, Test Adapters	16mm		RoHS
21101-221	Panhead Screw	Backplanes, Test Adapters	12mm		RoHS
21101-220	Panhead Screw	Backplanes, Test Adapters	10mm		RoHS
21101-219	Panhead Screw	Backplanes, Test Adapters	6mm		RoHS
21102-024	Panhead Screw		6mm	Metric	RoHS
21100-021	Panhead Screw	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	16mm		RoHS
21100-022	Panhead Screw	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	16mm		RoHS
21101-314	Panhead Screw	Backplanes, Test Adapters	5mm		RoHS
21100-650	Panhead Screw	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	16mm		RoHS

Katalogové číslo	Typ	Works With	Thread Length	Thread Type	Certifications
21101-069	Panhead Screw	Backplanes, Test Adapters	8mm		RoHS
21120-202	Panhead Screw	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	16mm		
21120-203	Panhead Screw	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	16mm		

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.