

Varistar CP Cabeling Rack



Welded steel frame for high static load requirements.
Prepared for high cable densities and 19" integration.

VLASTNOSTI

Preconfigured, ready to use cabinet

Static load-carrying capacity up to 1600 kg

Ingress protection class IP 20

Installation of different Networking equipment possible

Integrated vertical and horizontal cable management

Can be easily integrated into aisle containment system

Frame Material: Ocel
Materiál: Ocel
Product Type: Rack

SPECIFIKACE

Table 1/2

Katalogové číslo	Rack Height	Cladding Material	Frame Color	Výška	Frame Color Code	Cladding Color
10630-027	42U	Ocel	Black Grey	2000mm	RAL 7021	Black Grey
10630-028	42U	Ocel	Black Grey	2000mm	RAL 7021	Black Grey

Table 2/2

Katalogové číslo	Šířka	Hloubka	Static Load	Cladding Color Code	Množství v balení	Dynamic Load	Povrchová úprava
10630-027	800m m	1200m m	1600kg	RAL 7021	1	1000kgf	Strukturovaný Práškový
10630-028	800m m	1200m m	1600kg	RAL 7021	1	1000kgf	Strukturovaný Práškový

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.