

107 Wraparound Strap for CPVC Pipe

FUNKTIONER

Includes flared edges to protect piping

Rated for use with CPVC fire sprinkler pipe

Includes mounting screw



Materiale: Stål
Finish: Pregalvanized





SPECIFIKATIONER

Table 1/2

Katalognummer	Artikelnummer	NB/DN	Outer Diameter (OD)	Hole Size (HS)	A	B
1070075EG	597816	20	26.9 mm	5.8 mm	31.8 mm	60.3 mm
1070100EG	597817	25	33.7 mm	5.8 mm	36.5 mm	68.3 mm
1070125EG	597818	32	42.2 mm	5.8 mm	41.3 mm	77.8 mm
1070150EG	597819	40	48.3 mm	5.8 mm	44.5 mm	84.1 mm
1070200EG	597821	50	60.3 mm	5.8 mm	47.6 mm	93.7 mm

Table 2/2

Katalognummer	Artikelnummer	C	Hanger Spacing
1070075EG	597816	30.2 mm	1.65 m Max
1070100EG	597817	30.2 mm	1.8 m Max
1070125EG	597818	30.2 mm	1.95 m Max
1070150EG	597819	30.2 mm	2.1 m Max
1070200EG	597821	30.2 mm	2.4 m Max



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

