

108 Two Hole Strap for CPVC Pipe



FUNKTIONER

Includes flared edges to protect piping

Rated for use with CPVC fire sprinkler pipe

Includes mounting screws

Materiale: Stål
Finish: Pregalvanized





SPECIFIKATIONER

Table 1/2

Katalognummer	Artikelnummer	NB/DN	Outer Diameter (OD)	Hole Size (HS)	A	B
1080075EG	597822	20	26.9 mm	5.8 mm	82.6 mm	57.2 mm
1080100EG	597823	25	33.7 mm	5.8 mm	88.9 mm	63.5 mm
1080125EG	597824	32	42.2 mm	5.8 mm	108 mm	82.6 mm
1080150EG	597825	40	48.3 mm	5.8 mm	112.7 mm	87.3 mm
1080200EG	597826	50	60.3 mm	5.8 mm	125.4 mm	100 mm

Table 2/2

Katalognummer	Artikelnummer	C	Hanger Spacing
1080075EG	597822	30.2 mm	1.65 m Max
1080100EG	597823	30.2 mm	1.8 m Max
1080125EG	597824	30.2 mm	1.95 m Max
1080150EG	597825	30.2 mm	2.1 m Max
1080200EG	597826	30.2 mm	2.4 m Max



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

