

109 Side Mount Strap for CPVC Pipe



FUNKTIONER

Includes flared edges to protect piping

Rated for use with CPVC fire sprinkler pipe

Includes mounting screws

Materiale: Stål
Finish: Pregalvanized



SPECIFIKATIONER



Table 1/2

Katalognummer	Artikelnummer	NB/DN	Outer Diameter (OD)	Hole Size (HS)	A	B
1090075EG	597827	20	26.9 mm	5.8 mm	58.7 mm	42.9 mm
1090100EG	597828	25	33.7 mm	5.8 mm	66.7 mm	49.2 mm
1090125EG	597829	32	42.2 mm	5.8 mm	74.6 mm	58.7 mm
1090150EG	597831	40	48.3 mm	5.8 mm	81 mm	63.5 mm
1090200EG	597832	50	60.3 mm	5.8 mm	92.1 mm	76.2 mm

Table 2/2

Katalognummer	Artikelnummer	C	Hanger Spacing
1090075EG	597827	30.2 mm	1.65 m Max
1090100EG	597828	30.2 mm	1.8 m Max
1090125EG	597829	30.2 mm	1.95 m Max
1090150EG	597831	30.2 mm	2.1 m Max
1090200EG	597832	30.2 mm	2.4 m Max

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

