


2000 Beam Clamp Kit

FUNKTIONER

Light duty system

Includes clamp and U channel



Materiale: Stål
Finish: Electrogalvanized

SPECIFIKATIONER

Table 1/2

Katalognummer	Artikelnummer	Length (L)	A	B	C	D
2200EG	570140	200mm	25 mm	25 mm	65 mm	25 mm
2300EG	570160	300mm	25 mm	25 mm	65 mm	25 mm
2400EG	570180	400mm	25 mm	25 mm	65 mm	25 mm

Table 2/2

Katalognummer	Artikelnummer	E	Static Load 1 (F1)	Static Load 2 (F2)	Static Load 3 (F3)
2200EG	570140	30.5 mm	1700N	490N	340N
2300EG	570160	30.5 mm	1700N	490N	340N
2400EG	570180	30.5 mm	1700N	490N	340N


Height (H): 12 mm
Width (W): 25 mm
Thickness (T): 2 mm
Flange Thickness (FT): 11 mm Max
Hole Size (HS): 11 mm

Screw Diameter (Sc): 6
Torque (TQ): 30 N·m

YDERLIGERE PRODUKTOPLYSNINGER

For a secure grip the channel must extend to the outer edge of each beam clamp.

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

