

38 Offset Steel Eye Socket Rod Hanger



FUNKTIONER

Structural attachment used to join hanger rod to a structure

Provides full vertical rod adjustment



SPECIFIKATIONER

Table 1/2

Katalognummer	Artikelnummer	Materiale	Finish	Rod Size (RS)	Hole Size 1 (HS1)	Hole Size 2 (HS2)
038M0010EG	598290	Stål	Electrogalvanized	M10	13 mm	6.7 mm

Table 2/2

Katalognummer	Artikelnummer	Height (H)	Width (W)	C	D	Static Load
038M0010EG	598290	85 mm	29 mm	30.6 mm	19 mm	1112N

YDERLIGERE PRODUKTOPLYSNINGER

Load rating dependent on wood structure strength.

For 3/8" rod through 2" pipe, use two Model #43 Wood Drive Screws. For 3/8" rod through 4" pipe, use one Model #42 1/2" x 3" Lag Screw.



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

