

4G16 Twist Clip with Stud



FUNKTIONER

Supports electrical fixtures from acoustical T-grid

No tools required for installation

Fast, easy and secure twist-on installation

Nut sold separately

Materiale: Spring Stål;Stål



SPECIFIKATIONER


Table 1/2

Katalognummer	Artikelnummer	Finish	Farve	Flange Thickness (FT)	T-Grid Size	Screw Diameter (Sc)
4G16M11	178600	nVent CADDY Armour	Gray	1.5 mm	24mm	6
4G16M11WH	178620	Painted	White	1.5 mm	24mm	6
4G16M16	171900	nVent CADDY Armour	Gray	1.5 mm	24mm	6
4G16M16WH	576940	Painted	White	1.5 mm	24mm	6
4G16M25	176880	nVent CADDY Armour	Gray	1.5 mm	24mm	6
4G16M7	178590	nVent CADDY Armour	Gray	1.5 mm	24mm	6

Table 2/2

Katalognummer	Artikelnummer	Screw Length (L)	Static Load
4G16M11	178600	11mm	220N
4G16M11WH	178620	11mm	220N
4G16M16	171900	16mm	220N
4G16M16WH	576940	16mm	220N
4G16M25	176880	25mm	220N
4G16M7	178590	7mm	220N

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

