

APY External Horizontal Wall Bracket

FUNKTIONER

Side mount saddle support for C-Profiles and strut

Complete with fixings



SPECIFIKATIONER


Table 1/2

Katalognummer	Artikelnummer	Materiale	Finish	Channel Type	Strut Type	Height (H)
APYE01EG	584758	Stål	Electrogalvanized	E0L, E0, E1		40 mm
APYE23EG	584740	Stål	Electrogalvanized	E2L, E2, E3		40 mm
APYE4STRUTEG	584751	Stål	Electrogalvanized	E4	A (41 x 41 mm), C (21 x 41 mm)	50 mm
APYSTRUTS6	584840	Stainless Steel 316 (EN 1.4401)			A (41 x 41 mm), C (21 x 41 mm)	50 mm

Table 2/2

Katalognummer	Artikelnummer	Width (W)	Thickness (T)	A	B	C
APYE01EG	584758	124 mm	5 mm	31 mm	12 mm	19 mm
APYE23EG	584740	124 mm	5 mm	36 mm	12 mm	19 mm
APYE4STRUTEG	584751	144 mm	5 mm	43 mm	12 mm	19 mm
APYSTRUTS6	584840	144 mm	5 mm	43 mm	12 mm	19 mm

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

