


BSZ-M Concrete Screw



FUNKTIONER

Fire resistance class R30-R120 for design of anchorages under exposure to fire

ETA assessed for anchoring in cracked and non-cracked concrete

Use in concrete with threaded rod

Removable anchor is ideal for temporary fixings

Approved for use in seismic design category C1

Materiale: Stål
Finish: Electrogalvanized



SPECIFIKATIONER

Table 1/2


Katalognummer	Artikelnummer	Screw Length (L)	Rod Size (RS)	Hex Dimension	Drill Bit Diameter	Drill Bit Diameter
BSZM6X35EG	402690	35mm	8, 10	13mm	6mm	6mm
BSZM6X55EG	402695	55mm	8, 10	13mm	6mm	6mm

Table 2/2

Katalognummer	Artikelnummer	Embedment Depth	Torque (TQ)
BSZM6X35EG	402690	35 mm	10 N·m
BSZM6X55EG	402695	55 mm	10 N·m

Characteristic Axial Loads from ETA-20/0046

Part Number	Cracked Concrete C20/25	Non-Cracked Concrete C20/25	Standard Embedment Depth
BSZM6X35EG	1.81 kN	1.98 kN	35 mm
BSZM6X55EG	4.62 kN	6.61 kN	55 mm



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

