

C-EC Cable to Strut Clamp



FUNKTIONER

One-piece cable/conduit clamp with protective boot

No screws or bolts to drop

Requires only a screwdriver or nutdriver for installation

Fits into open side of strut channel

Materiale: Stål
Finish: Hot-Dip Galvanized

SPECIFIKATIONER




Katalognummer	Artikelnummer	Outer Diameter (OD)	Width (W)	Thickness (T)	Torque (TQ)	A	B
C12EC	337600	8 - 12 mm	20 mm	1.5 mm	2 N·m	18 mm Min	10 mm Max
C16EC	337610	12 - 16 mm	20 mm	1.5 mm	2 N·m	18 mm Min	10 mm Max
C20EC	337620	16 - 20 mm	20 mm	1.5 mm	2 N·m	18 mm Min	10 mm Max
C24EC	337630	20 - 24 mm	20 mm	1.5 mm	2 N·m	18 mm Min	10 mm Max
C28EC	337640	24 - 28 mm	20 mm	1.5 mm	2 N·m	18 mm Min	10 mm Max
C32EC	337650	28 - 32 mm	25 mm	1.75 mm	2 N·m	18 mm Min	10 mm Max
C36EC	337660	32 - 36 mm	25 mm	1.75 mm	2 N·m	18 mm Min	10 mm Max

Katalognummer	Artikelnummer	Outer Diameter (OD)	Width(W)	Thickness(T)	Torque(TQ)	A	B
C40EC	337670	36 - 40 mm	25 mm	1.75 mm	2 N·m	18 mm Min	10 mm Max
C44EC	337680	40 - 44 mm	25 mm	2 mm	4 N·m	18 mm Min	10 mm Max
C48EC	337690	44 - 48 mm	25 mm	2 mm	4 N·m	18 mm Min	10 mm Max
C52EC	337700	48 - 52 mm	25 mm	2 mm	4 N·m	18 mm Min	10 mm Max
C56EC	337710	52 - 56 mm	25 mm	2 mm	4 N·m	18 mm Min	10 mm Max
C60EC	337720	56 - 60 mm	30 mm	2.25 mm	4 N·m	18 mm Min	10 mm Max
C64EC	337730	60 - 64 mm	30 mm	2.25 mm	4 N·m	18 mm Min	10 mm Max

YDERLIGERE PRODUKTOPLYSNINGER

Screw is electrogalvanized on clamps that have an outer diameter of 40 mm or less.

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

