

CHN Chain

FUNKTIONER

Round link chain

Conforms to DIN 5685



SPECIFIKATIONER

Table 1/2


Katalognummer	Artikelnummer	Materiale	Finish	Length (L)	A	B
CHN13K	386780	Stål	Electrogalvanized	30m	22 mm	3.5 mm
CHN13KSP	591410	Stål	Electrogalvanized	100m	22 mm	3.5 mm
CHN15K	385910	Stål	Electrogalvanized	30m	24 mm	4.5 mm
CHN15KS4	591500	Stainless Steel 304 (EN 1.4301)		30m	24 mm	4.5 mm
CHN17K	385920	Stål	Electrogalvanized	30m	26 mm	5.5 mm
CHN17KS4	591510	Stainless Steel 304 (EN 1.4301)		30m	26 mm	5.5 mm

Table 2/2

Katalognummer	Artikelnummer	D	Static Load	Certificeringer
CHN13K	386780	2 mm	200N	ITB
CHN13KSP	591410	2 mm	200N	
CHN15K	385910	2.5 mm	300N	ITB
CHN15KS4	591500	2.5 mm	300N	ITB

Katalognummer	Artikelnummer	D	Static Load	Certificeringer
CHN17K	385920	3 mm	400N	ITB
CHN17KS4	591510	3 mm	400N	ITB

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

