

Drop-In Anchor



FUNKTIONER

Internal thread provides easy removal and serviceability

Installs flush or below the base surface

Suitable for redundant non-structural systems on cracked and non-cracked concrete

Fire resistance class R30-R120 for design of anchorages under exposure to fire




SPECIFIKATIONER

Katalognummer	Artikelnummer	Materiale	Finish	Hole Size (HS)	Length (L)	Drill Bit Diameter	Certificeringer
CAM10040	593200	Stål	Electrogalvanized	10 mm	40mm	12mm	VdS, CE, 14-0135, FM Approved, Anchor, CE, 14-0068
CAM10040S6	401155	Stainless Steel 316 (EN 1.4401)		10 mm	40mm	12mm	CE, 14-0068, VdS
CAM12050	400415	Stål	Electrogalvanized	12 mm	50mm	15mm	CE, 14-0068, FM Approved, Anchor, CE, 14-0135, VdS
CAM6030	593180	Stål	Electrogalvanized	6 mm	30mm	8mm	CE, 14-0068, CE, 14-0135
CAM8030	593190	Stål	Electrogalvanized	8 mm	30mm	10mm	VdS, CE, 14-0068, CE, 14-0135
CAM8030S6	401154	Stainless Steel 316 (EN 1.4401)		8 mm	30mm	10mm	CE, 14-0068, VdS

Characteristic Axial Loads from ETA 14-0135			
Part Number	Cracked Concrete C20/25	Non-Cracked Concrete C20/25	Standard Embedment Depth
CAM6030	-	2.50 kN	25 mm
CAM8030	-	3.30 kN	30 mm
CAM10040	-	4.40 kN	40 mm
CAM12050	-	6.10 kN	50 mm
CAM8030S6	-	-	-
CAM10040S6	-	-	-

Characteristic Axial Loads from ETA 14-0068 - for redundant non-structural systems			
Part Number	Cracked Concrete C20/25	Non-Cracked Concrete C20/25	Standard Embedment Depth
CAM6030	0.80 kN	0.80 kN	25 mm
CAM8030	1.20 kN	1.20 kN	30 mm
CAM10040	1.70 kN	1.70 kN	40 mm
CAM12050	2.60 kN	2.60 kN	50 mm
CAM8030S6	1.20 kN	1.20 kN	25 mm
CAM10040S6	1.70 kN	1.70 kN	40 mm

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

