

EER-Ti/T Trapezoidal Deck Threaded Rod Hanger



FUNKTIONER

Supports threaded rod

Thread impression for simple installation

Materiale: Spring Steel
Finish: nVent CADDY Armour



SPECIFIKATIONER

Table 1/2

Katalognummer	Artikelnummer	Hole Size (HS)	Hole Type	Flange Thickness (FT)	Drill Bit Diameter	Static Load 1 (F1)
EERTIM10	173140	10 mm	Threaded	0.8 - 3 mm	7mm	450N
EERTIM6	173120	6 mm	Threaded	0.8 - 3 mm	7mm	450N
EERTIM8	173130	8 mm	Threaded	0.8 - 3 mm	7mm	450N


Table 2/2

Katalognummer	Artikelnummer	Static Load 2 (F2)	Certificeringer
EERTIM10	173140	900N	ITB
EERTIM6	173120	900N	
EERTIM8	173130	900N	ITB

YDERLIGERE PRODUKTOPLYSNINGER

Static Load 1 represents 0.8 - 2.0 mm flange thickness. Static Load 2 represents 2.0 - 3.0 mm flange thickness.

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDD1

