

38 Offset Steel Eye Socket Rod Hanger, M10 Rod



KATALOGNUMMER

038M0010EG

FUNKTIONER

Structural attachment used to join hanger rod to a structure

Provides full vertical rod adjustment



PRODUKTEGENSKABER

Artikelnummer: 598290

Materiale: Stål

Finish: Electro galvanized

Rod Size (RS): M10

Pipe Size: 100" Max

Hole Size 1 (HS1): 13 mm

Hole Size 2 (HS2): 6.7 mm

Height (H): 85 mm

Width (W): 29 mm

C: 30.6 mm

D: 19 mm



Static Load: 1112N

YDERLIGERE PRODUKTOPLYSNINGER

Load rating dependent on wood structure strength.

For 3/8" rod through 2" pipe, use two Model #43 Wood Drive Screws. For 3/8" rod through 4" pipe, use one Model #42 1/2" x 3" Lag Screw.

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

