

310M Universal Beam Clamp, Thick Flange, M12 Hole, Threaded, 31.8 mm Max Flange



KATALOGNUMMER

310M12

FUNKTIONER

Universal beam clamp for thick beams



PRODUKTEGENSKABER

Artikelnummer: 388890

Materiale: Cast Iron

Finish: Electrogalvanized

Hole Size (HS): 12 mm

Hole Type: Threaded

Flange Thickness (FT): 31.8 mm Max

A: 28.6 mm


Torque (TQ): 15 N·m

Static Load 1 (F1): 4200N

Static Load 2 (F2): 3300N

YDERLIGERE PRODUKTOPLYSNINGER

Setscrew must be tightened and torqued onto the sloped side of the I-beam.



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

