

# 4G24H Twist Clip with 90° Plain Hole, CADDY ARMOUR, Gray, 5.8 mm Hole, 1.5 mm Max Flange, 24 mm T-Grid



## KATALOGNUMMER

**4G24H**

## FUNKTIONER

Provides an attachment for nVent CADDY Speed Link assemblies, wire, S-hooks, or chain from T-Grid

Fast, easy and secure twist-on installation

Designed to reduce scratching of T-grid

No tools required for installation



## PRODUKTEGENSKABER

Artikelnummer: 170490

Materiale: Spring Steel

Finish: nVent CADDY Armour


Farve: Gray

Hole Size (HS): 5.8 mm

Flange Thickness (FT): 1.5 mm Max

T-Grid Size: 24mm

Static Load: 180N



## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

