


4G24H Twist Clip with 90° Plain Hole, Painted, White, 5.8 mm Hole, 1.5 mm Max Flange, 24 mm T-Grid



KATALOGNUMMER

4G24HWHSP25

FUNKTIONER

Provides an attachment for nVent CADDY Speed Link assemblies, wire, S-hooks, or chain from T-Grid

Fast, easy and secure twist-on installation

Designed to reduce scratching of T-grid

No tools required for installation



PRODUKTEGENSKABER

Artikelnummer: 172280

Materiale: Spring Steel

Finish: Painted


Farve: White

Hole Size (HS): 5.8 mm

Flange Thickness (FT): 1.5 mm Max

T-Grid Size: 24mm

Static Load: 180N



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

