

Multi-Function Clip, M4, M10 Rod, 4.8 mm Wire, 3–9.5 mm Flange, 6.5 mm Hole



KATALOGNUMMER

4Z34

FUNKTIONER

Provides attachment of electrical boxes

Supports #10-24 and 1/4-20 (M6) threaded bridle rings

Instills more confidence installing conduit, MC/AC, and low voltage applications



PRODUKTEGENSKABER

Artikelnummer: 170650

Materiale: Spring Steel

Finish: nVent CADDY Armour

Rod Size (RS): M4;M6;M8;M10

Trådstørrelse: 3.9 - 4.8 mm

Flange Thickness (FT): 3.0 - 9.5 mm

Hole Size (HS): 6.5 mm

Screw Included: No


Static Load 1 (F1): 110N

Static Load 2 (F2): 90N

YDERLIGERE PRODUKTOPLYSNINGER

NEC® 300.11 requires dedicated drop wire/rod and EC311.

4Z parts installed on 3/8" (M10) smooth rod in the F2 direction has a Static Load Rating of 15 lb (67 N).



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

