


Strut Channel Type A, Slotted, Steel, Hot-dip galvanized, 3m long 41x41x1.5 mm

KATALOGNUMMER

A15L3000HD



FUNKTIONER

Cold formed channel, slotted

Strut channels for heavy applications

For individual fastening or for efficiently constructing pipe or tube routes



PRODUKTEGENSKABER

Artikelnummer: 317241

Strut Type: A (41 x 41 mm)

Materiale: Stål

Finish: Hot-Dip Galvanized

Thickness (T): 1.5 mm

Length (L): 3000mm

Height (H): 41 mm



Width (W): 41 mm

A: 22.3 mm

B: 11 mm

C: 27 mm

D: 50 mm



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

