

C-Channel Beam Clamp with U-Bolt, E0L, E0, E1, E2L, E2, E3 Channel, M6 Rod



KATALOGNUMMER

BCE03

FUNKTIONER

Beam clamp for C-Profiles

Complete with plate, U-bolt and fixings

PRODUKTEGENSKABER

Artikelnummer: 585120

Materiale: Stål

Finish: Electrogalvanized

Channel Type: E0L;E0;E1;E2L;E2;E3

Rod Size (RS): 6

Flange Thickness (FT): 16 mm Max

Width (W): 60 mm

Thickness (T): 4 mm

A: 20 mm

B: 36 mm


C: 70 mm

Static Load: 1250N

YDERLIGERE PRODUKTOPLYSNINGER

Static Load is dependent on channel type and length.

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

