

C-EC Cable to Strut Clamp, 8–12 mm OD



KATALOGNUMMER

C12EC

FUNKTIONER

One-piece cable/conduit clamp with protective boot

No screws or bolts to drop

Requires only a screwdriver or nutdriver for installation

Fits into open side of strut channel

PRODUKTEGENSKABER

Artikelnummer: 337600

Materiale: Stål

Finish: Hot-Dip Galvanized

Outer Diameter (OD): 8 - 12 mm

Width (W): 20 mm

Thickness (T): 1.5 mm

Torque (TQ): 2 N·m




A: 18 mm Min

B: 10 mm Max

YDERLIGERE PRODUKTOPLYSNINGER

Screw is electrogalvanized on clamps that have an outer diameter of 40 mm or less.

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

