

C-EU Single Cable to Flange Clamp, 12–16 mm OD, 12 mm Max Flange, 46 mm Max



KATALOGNUMMER

C16EU

FUNKTIONER

Supports single run of conduit

Attaches to beam flanges, angle iron, joists and other structural supports

PRODUKTEGENSKABER

Artikelnummer: 337310

Materiale: Stål

Finish: Hot-Dip Galvanized

Outer Diameter (OD): 12 - 16 mm



Flange Thickness (FT): 12 mm Max

A: 46 mm Max

Torque (TQ): 2 N·m

YDERLIGERE PRODUKTOPLYSNINGER

Screw is electrogalvanized on clamps that have an outer diameter of 40 mm or less.



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

