

Multi-Function C-Clamp, Steel, Hot-dip galvanized, 4–20 mm Flange



KATALOGNUMMER

C20HD

FUNKTIONER

Multi-functional beam clamp

Use with Cable/Conduit/Pipe Clamp or Square Washer for Multi-Function C-Clamp

PRODUKTEGENSKABER

Artikelnummer: 336100

Materiale: Stål

Finish: Hot-Dip Galvanized

Flange Thickness (FT): 4 - 20 mm

Hole Size (HS): 14 mm

Screw Diameter (Sc): 6


Screw Length (L): 25mm

Torque (TQ): 3 N·m

Static Load: 1100N

YDERLIGERE PRODUKTOPLYSNINGER

Setscrew must be tightened and torqued onto the sloped side of the I-beam.



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

