

Cat HP J-Hook Mod Clip for M4-M12 Threaded Rod, 4,8 - 6,4mm Wire



KATALOGNUMMER

CATHPM4Z34

Improved nVent CADDY Cat HP Mod Clip J-Hook with Rod/Wire Clip allows for quick attachment to threaded rod or wire without screws or special tools. Enjoy enhanced stability and customization for efficient cable management while gaining ultimate flexibility on the job and minimizing inventory impact.

FUNKTIONER

Tool-free assembly

Works with nVent J-Hook Versa-Mount technology from nVent CADDY



PRODUKTEGENSKABER

Artikelnummer: 186082


Finish: nVent CADDY Armour

Materiale: Spring Steel

Rod Size (RS): M4;M6;M8;M10;M12

Trådstørrelse: 4.8 - 6.4 mm

Static Load: 130N



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

