

# Branch Line Restraint Structure Attachment to Steel, M10, M12 Rod

## KATALOGNUMMER

**CSBBRS1MEG**

## FUNKTIONER

Swivel barrel nut accepts 3/8" or 1/2" (M10 or M12) threaded rod

Attaches to steel members with self-drilling/tapping screw



## PRODUKTEGENSKABER

Artikelnummer: 402239

Materiale: Stål

Finish: Electro galvanized

Rod Size (RS): 10;12

Flange Thickness (FT): 2.7 - 12.7 mm

Height (H): 28.2 mm

Length (L): 40.4mm


Width (W): 26.9 mm

Screw Diameter (Sc): 2.7 mm

Screw Length (L): 32mm

## YDERLIGERE PRODUKTOPLYSNINGER

Branch line structural attachments are for restraint only and not for the hanging of fire sprinkler piping.



## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

