

Branch Line Restraint Structure Attachment to Wood/Concrete, M10, M12 Rod

KATALOGNUMMER

CSBBRS2MEG

FUNKTIONER

Swivel barrel nut accepts 3/8" or 1/2" (M10 or M12) threaded rod

Attaches to wood or concrete where cracked concrete approval is not needed



PRODUKTEGENSKABER

Artikelnummer: 402240

Materiale: Stål

Finish: Electro galvanized

Rod Size (RS): 10;12

Height (H): 28.2 mm

Length (L): 40.4mm

Width (W): 26.9 mm


Screw Diameter (Sc): 1/4"

Screw Length (L): 44.5mm

Drill Bit Diameter: 5mm

YDERLIGERE PRODUKTOPLYSNINGER

Branch line structural attachments are for restraint only and not for the hanging of fire sprinkler piping.



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

