

Hammer-On Flange Clip, Bottom Mount, Spring Steel, 14–20 mm Flange M6 Rod



KATALOGNUMMER

EM912

FUNKTIONER

Can be used to support boxes, fixtures or other applications from beam flanges

Assorted attachment points provided to reduce inventory

Requires only a hammer to install



PRODUKTEGENSKABER

Artikelnummer: 170070

Materiale: Spring Steel

Finish: nVent CADDY Armour



Flange Thickness (FT): 14 - 20 mm

Rod Size (RS): 6

Static Load 1 (F1): 450N

Static Load 2 (F2): 110N

Static Load 3 (F3): 330N



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

