

FCS Height Adjustable Loop Hanger, 1 1/2" Pipe, DN40, 48 mm, M10 Rod



KATALOGNUMMER

FCS0150M10

FUNKTIONER

Recommended for the suspension of stationary non-insulated fire sprinkler pipe

Redesigned strap and cup nut minimize friction for easier adjustment up and down the threaded rod (1/2" to 4" sizes)

Formed tips on the upper strap simplify disassembly and reassembly of the hanger

Rolled edges on the strap help to guide the pipe through, limiting binding and damage to metal or plastic pipe

Package includes all necessary hardware for installation



PRODUKTEGENSKABER

Artikelnummer: 597972

Materiale: Stål

Finish: Electrogalvanized

Pipe Size: 1 1/2"

NB/DN: 40

Outer Diameter (OD): 48 mm

Rod Size (RS): M10

Width (W): 10 mm


A: 99 mm

B: 41 mm

C: 17 mm

Static Load: 2000N

Wrench Size: 15 mm



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

